

AZM100

Advance Zoom Stereoscopy



LABO®

Worlds Within™

SPECIFICATIONS



STAND	Dual Light stand with Ball bearing focusing controls and built in slip clutch
ILLUMINATION	Built in illumination both for incident light 15W Halogen, with variable intensity control and sub-stage transmitted fluorescent lamp 5 W. Both lights can be used individually or simultaneously.
VIEWING BODIES	Binocular Zoom Pod 1: 9.2, Mag.6.5x-60x, inclined at 45°, 360° rotatable, IPD 48-75mm, Trinocular Zoom Pod 1: 9.2, Mag. 6.5x-60x, inclined at 45°, 360° rotatable, IPD 48-75mm
EYEPIECE	WF10x/ 23mm with Eye-guards. Anti Mould Treated. Optional WF 15x/16mm, WF 20x/12mm
AUXILIARY OBJECTIVES	0.5x, 1.5x and 2.0x (Optional)
ACCESSORIES	Darkfield attachment, Polarizing Kit, Ring Light, Fiber Optic illumination, Single/Dual Light guides, Photo adapters for CCD Camera/35mm SLR Camera/Digital still camera and Soft carrying case



www.labomicrosystems.com

USA Facility:
LABO Microsystems
6960-A Camino Maquiladora
San Diego, CA 92154, USA.
Tel : +1 604 944 0622, Fax: +1 604 608 3225
Tel Toll Free USA/Canada 1 877 650 0117
E-mail: sales@labomicrosystems.us

German Facility:
LABO Microsystems GmbH
Bäckerstrasse 5
21244 Buchholz, Germany
Tel: + 49 4181 9906360
Fax: + 49 4181 9906369
E-mail: hq@labomicrosystems.com

Global Sales:
LABO Microsystems
P.O. Box 213671, Jumeirah, Dubai.
United Arab Emirates.
Tel: + 97 150 242 0048
Tel: + 91 941 666 6666
E-mail: labo@labomicrosystems.com

